



The palm grip B9 has different equipment options for many requirements. It is compatible with our multi-axis controller or mounted on hydraulic drives. The palm grip has a highly flexible single wire (0,1mm², 450mm long). The mounting piece for the drive rod can be supplied with a tapped hole 12mm (standard) or 10mm.

Technical data

Operating temperature	-40°C to +60°C
Degree of protection	IP65
Contact complement	1,5A 24V DC13



PA11

÷

PA13

A13

Example

КΤ

- 2D

Basic	unit
Basic B9	Palm grip
Digita	actuating element
D	Push button
	Colour: red, black, yellow, green, blue, white
KT	Cross switch T-0-T/T-0-T
KR	Cross switch R-0-R/R-0-R
A11	Rocker switch T-0-T Pos. 11+12
A11	Rocker switch R-0-R Pos. 11+12
A13	Rotary grip T-0-T
Analo	g actuating element
V21	Hall-minijoystick (see page 61)
	Output 0,52,54,5V inverse dual
PA11	Rocker analog Pos. 11+12
	Potentiometer T394 2x5kOhm with direction contacts
H11	Rocker analog Pos. 11+12
	Hall-Potentiometer
	Output 0,52,54,5V inverse dual
PA13	Rotary grip
	Potentiometer T375 2x5kOhm with direction contacts
H13	Hall-Rotary grip
	Output 0,52,54,5V inverse dual
Speci	al model
Х	Special / customer specified

B9

Attachments			
Z01	Bellow KMD 109	10300009	
Z02	Bellow KMD 190	10300093	
Z03	Rosette KBF 905 with 4 screws M5x15 necessary for bellow KMD 190	5209900404	

2

- X

1.1

Technical details may vary based on configuration or application! Technical data subject to change without notice!


Palm grip B9





B9

2


Edition : Push button installed Pos. 1 - 8 Cross switch tast







Edition : Push button installed Pos. 1 - 8 Multi-axis controller V21



Technical details may vary based on configuration or application! Technical data subject to change without notice!